


MINISM@RT LOOSETUBE

External Mini Loose Tube Optical Cable for use in micro ducts

Cable Design

**IEC 60794-5
ACMA - AS/CA S008**



- Drawing not to scale -

- **Multi-loose tube construction** – Single layer 2 to 144 fibres
- **Central strength member (CSM):** Glass fibre reinforced plastic material (GRP) with or without over-sheathing
- **Tube:** Thermoplastic material, containing up to 12 optical fibres filled with a low viscosity, thixotropic, non-melting gel fully compatible with fibre coating and tube material
- **Stranding:** The required numbers of elements (tubes and fillers) are SZ stranded around the central strength member
- **Longitudinal water tightness:** Water swellable elements (dry-core)
- **Sheath:** UV stabilised polyethylene in compliance with AS 1049. Two ripcords provided beneath the sheath for easy removal
- **Outer jacket:** UV stabilised polyamide (Nylon) in compliance with AS 1049 integrally bonded to PE sheath

This loose tube dielectric optical cable is designed for external underground installations in (micro) ducts by pulling, blowing or floating techniques. Polyamide provides anti-termite protection. Optimised for blowing in mini ducts of 10mm diameter (internal).

Technical data

Number of Fibres		2 to 72	96	144
Number of elements		6	8	12
Tube / Filler diameter	mm	1.55		1.35
Cable nominal diameter	mm	6.3	7.4	8.4
Cable nominal weight	kg/km	33	49	62
Max. installation tension	kN	1.0	2.0	2.0
Max. crush resistance	kN/100mm	2.0	2.0	2.0
Min. bending radius				
At full load		130	220	220
At no load	mm	65	110	110
Temperature range	°C	Installation -0 -> +50	Transport & Storage -20 -> +70	Operation -10 -> +70

Optical Characteristics

See the attached cabled optical fibre data sheet.

Identification

Fibre and Buffer Tube Colours

No.	1	2	3	4	5	6	7	8	9	10	11	12
Colour	blue	orange	green	brown	grey	white	red	black	yellow	violet	pink	aqua

Fillers are either natural (opaque) or black.

Sheath Colour:

The outer sheath colour is blue.

Sheath Marking:

The outer sheath is marked in 1 metre intervals as follows:

PRYSMIAN DW MINISM@RT DUCT Part Number T/N ##### MM/YY MADE IN AUSTRALIA *****M >> | << *****M

Main mechanical characteristics

Parameter	Test method	Test conditions	Acceptance criteria*
Tensile strength	IEC 60794-1-21-E1	Load: As per cable maximum installation tension in technical data table above	Fibre strain \leq 0.6%. No physical damage and no change in attenuation after test.
Crush	IEC 60794-1-21-E3	Load: As per maximum crush resistance in technical data table above Duration: 10 min	No physical damage. No change in attenuation after test.
Impact	IEC 60794-1-21-E4	Impact energy: 1 J Anvil radius: 300 mm	No physical damage. No change in attenuation after test.
Torsion	IEC 60794-1-21-E7	Sample length: 1 m Rotation: +/-180 degree, 10 cycles	No physical damage. No change in attenuation after test.
Bend	IEC 60794-1-21-E11	Mandrel radius: As per Min. bending radius at no load in technical data table above No. of turns/helix: 4, No. of cycles: 3	No physical damage. No change in attenuation after test.
Bend under tension	Concurrent to tensile test	Mandrel radius: As per Min. bending radius at full load in technical data table above Bend: 360°, 1 turn	No physical damage. No change in attenuation after test.
Temperature cycling	IEC 60794-1-22-F1	Sample length: 1000 m (minimum) Temperature range: As per Operation temperature range in technical data table above	No change in attenuation between 10°C & 30°C. Max. change in attenuation \leq 0.15dB/km between Min. & Max. operation temperatures.
Cable aging	IEC 60794-1-22-F9	85°C for 168 h followed by Temperature cycling	Max. change in attenuation \leq 0.10dB/km after test
Water penetration	IEC 60794-1-22-F5C	Sample length=3m, Water height=1m	No water leakage after 24 hours

* All optical measurements for singlemode fibres performed at 1550 nm.

Logistic

Packing:

Timber drums to AS/NZS 2857 with flexible cable wrap protection

Delivery Lengths:

Standard delivery length is 4 km with a tolerance of - 1% / + 3%

© PrysmianGroup 2012, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by PrysmianGroup: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of PrysmianGroup. The information is believed to be correct at the time of issue. PrysmianGroup reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by PrysmianGroup.