

# Sound the alarm!

Our fire alarm cables will get the message through.



A brand of the

**Prysmian**  
Group

# Our fire alarm cables will get the message through.

No matter what fire detection system you will install, you can rest assured our fire alarm cables will connect every piece of hardware and transfer the signals. We have solutions for both conventional and addressable systems as well as for detectors and speaker circuits. Keep calm, all systems go.

## Range features:

- Easy strip sheath for ease of termination & installation.
- Mechanical protection rating – WSX1.
- Available in 200m and 500m rolls.
- Compliant with Marking requirements of AS1670.2015.
- AS/CA S008 Compliant.
- GBCA – PVC best practice certification.
- Meter Marked.

## 2C Flat – 250/250V

Suitable for cabling from Conventional Fire Alarm, OWS & EWIS panels, to detectors and speakers, strobes, horns, field modules.



Item number	Core Size	Insul'n/sheath Thickness	Overall size
20271379	1.0	0.6/0.8	6.7 x 4.3
20257705	1.5	0.6/0.8	7.3 x 4.6

## 2C Flat White Stripe – 250/250V

White Stripe Flat TPS complies with the requirements of AS1670.2015 to distinguish Speaker Circuits from ELV cables. Suitable for Cabling of Speaker circuits.



Item number	Core Size	Insul'n/sheath Thickness	Overall size
20271380	1.0	0.6/0.8	6.7 x 4.3
20267579	1.5	0.6/0.8	7.3 x 4.6

## 2C Twisted – 250/250V

Cabling between Addressable fire panels, detectors and devices.



Item number	Core Size	Insul'n/sheath Thickness	Overall size
20257706	1.5	0.6/0.8	7.2

## 2C Twisted Screened – 250/250V

Suitable for VESDA and other communication networks.



Item number	Core Size	Insul'n/sheath Thickness	Overall size
20234676	1.5	0.6/0.8	7.4



All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group; any modification or alteration afterwards of product may give different result. The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.

