

CONSTRUCTION - XLPE CABLES 0.6/1 kV









2C+E XLPE CIRCULAR

X-90 XLPE INSULATED LAID UP AND PVC SHEATHED CABLE TO AS/NZS 5000.1.

For mains, submains and subcircuits unenclosed, in conduit, buried direct or in underground ducts for buildings and industrial plants where not subject to mechanical damage. Suitable where space is at a premium and/or where conditions of overload may occur.



Cable Characteristics

							
Semi-rigid	OD≤25 4D OD>25 6D	1	Water Drops	Good	+90 °C -15 °C	C3	Good

Cable Design

CONDUCTOR:

Plain annealed copper conductor to AS/NZS 1125
 Maximum continuous operating temperature: 90 °C











INSULATION:

V-90 XLPE
 Colours: Red, Black, Green/Yellow

SHEATH:

5V-90 PVC
 Colours: Orange

Installation Conditions

							
INDUSTRIAL EQUIPMENT	OD≤25 6D OD>25 9D	IN FREE AIR	IN CONDUIT	MACHINES	0 °C	IN TRENCH	IN GROUND WITH PROTECTION
							
IN DUCT	EXTERNAL BUILDING						

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group; any modification or alteration afterwards of product may give different result. The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.



Physical & Electrical Characteristics

Product code	Conductor			Cable				Min. installed bending radius mm
	Nominal C.S.A. mm ²	Number and diameter of wires No/mm	Nominal diameter mm	Nominal insulation thickness mm	Overall diameter mm		Approx. mass kg/100 m	
					Minimum	Maximum		
1.52CEXP	1.5	7/0.50	1.5	0.7	9.6	10.4	15	42
2.52CEXP	2.5	7/0.67	2.0	0.7	10.8	11.7	20	47
42CEXP	4	7/0.85	2.6	0.7	11.6	12.5	25	50
62CEXP	6	7/1.04	3.1	0.7	12.6	13.6	30	54
102CEXP	10	7/1.35	4.1	0.7	14.4	15.4	42	62
162CEXP	16	7/1.70	5.1	0.7	16.8	17.7	55	71

Conductor nominal C.S.A. mm ²	Current rating (a)			Electrical characteristics	
	Unenclosed spaced A	Buried direct A	Underground in duct A	Maximum D.C. resistance at 20°C Ω/km	Reactance per core Ω/km
1.5	24	33	25	13.6	0.107
2.5	34	46	35	7.41	0.0988
4	45	60	46	4.61	0.0930
6	57	75	57	3.08	0.0887
10	78	100	77	1.83	0.0840
16	105	130	100	1.15	0.0805


(a) Based on 90 °C conductor temperature, 40 °C ambient air temperature and where applicable, burial depth of 0.5 m, soil temperature of 25 °C and soil thermal resistivity of 1.2 °C.m/W. Refer to AS/NZS 3008.1 for other installation conditions.

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group; any modification or alteration afterwards of product may give different result. The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.




CABLE HANDLING

Cable Usage Characteristics




AMBIENT TEMPERATURE

Maximum operating temperature
Minimum operating temperature




MECHANICAL IMPACT RESISTANCE

1	Light Impact
2	Moderate Impact
3	Heavy Impact
4	Very Heavy Impact




RESISTANCE TO SOLAR RADIATION AND WEATHER

Excellent	Permanent
Very Good	Frequent
Good	Occasional
Acceptable	Accidental
Poor	None




BEHAVIOUR IN FLAME AND FIRE

Reaction To Fire	Resistant To Fire
C 1 Fire retardant	Level 1 Ultimate fire survival
C 2 Flame retardant	Level 2 Two hours fire survival
C 3 No fire performance	Level 3 Restrained spread & self extinguishing




HALOGEN FREE

AS/NZS 4507




MINIMUM BENDING RADIUS

Minimum bending radius of installed cables
--




CHEMICAL RESISTANCE

Excellent	Permanent
Very Good	Frequent
Good	Occasional
Acceptable	Accidental
Poor	None




RESISTANCE TO WATER

Negligible	No humidity
Water Drops	Occasional condensation
Spray	Water run off
Splashes	Exposed to water splashes
Heavy Sea	Exposed to waves
Immersion	Temporarily covered by water
Submersion	Permanently covered by water



FLEXIBILITY



















Rigid	Flexible
Semi-rigid	Very flexible



LOW SMOKE EMISSION

AS/NZS 4507

Laying Conditions

 MINIMUM BENDING RADIUS DURING INSTALLATION	 IN TRENCH	 IN GROUND	 IN DUCT	 DOMESTIC APPLIANCES	 MACHINES
 MOBILE EQUIPMENT	 SUBMERGED	 OVERHEAD AERIAL	 MIN. INSTALLATION TEMPERATURE	 IN FREE AIR	 IN GROUND WITH PROTECTION
 IN CONDUIT	 OUTDOOR APPLIANCES	 FESTOON	 INTERNAL WIRING	 INDUSTRIAL EQUIPMENT	 EXTERNAL BUILDING

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group; any modification or alteration afterwards of product may give different result. The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.

