


AIR CONDITIONING CABLES

PVC FLAT 450/750 V



Cable description:

3 Core plus Earth Flat TPS Cable, Copper Conductor, V-90 PVC Insulated and 3V-90 PVC Sheathed, to AS/NZS 5000.2.



Cable description	Nominal conductor area mm ²	Approx. overall diameter mm	Approx. mass kg/100 m	Min. installed bending radius mm	Cores construction/ Sheat colour
3C+E		3C+E	3C+E	3C+E	
Applications: 3 phase					
1.53CEF RWBU/BU AIRCON	1.5	12.8 x 4.6	12	20	Blue-Red-G/Y-White/Blue
2.53CEF RWBU/BU AIRCON	2.5	15.8 x 5.5	19	20	Blue-Red-G/Y-White/Blue
Applications: fixed installations					
1.53CEF RWBK/BU AIRCON	1.5	12.8 x 4.6	12	20	Black-Red-G/Y-White/Blue
2.53CEF RWBK/BU AIRCON	2.5	15.8 x 5.5	19	20	Black-Red-G/Y-White/Blue

3C+E = 3 Core + Earth.

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group; any modification or alteration afterwards of product may give different result. The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.



3-PHASE CURRENT RATINGS

3 CORE (CU) 75°C

Cable description:

3 Core LV, Non Flexible, Copper Conductor, Insulated and Sheathed (including neutral screened) Cables with or without Earth Conductor, Armoured or Non-Armoured Cables with V-75, V-90, V-90HT PVC, HFI-75-TP or HFI-90-TP LSOH Insulation. Based on AS/NZS 3008.1.1.

Nominal conductor area mm ²	Unenclosed			Enclosed Wiring enclosure in air	Unenclosed thermal insulation		Buried direct	Underground wiring enclosure	Three phase voltage drop (@ 50Hz & 75°C) mV/A.m
	Spaced	Touching	Exposed to sun		Partially surrounded by thermal insulation	Completely surrounded by thermal insulation			
1.0	13	12	9	11	9	6	14	14	44.7
1.5	16	15	12	14	12	8	18	18	28.6
2.5	23	22	17	20	17	11	25	25	15.6
4	31	29	23	25	23	15	33	33	9.71
6	40	37	29	33	30	19	42	42	6.49
10	54	51	39	44	41	25	55	55	3.86
16	72	68	51	58	54	34	96	73	2.43
25	97	91	67	76	73	46	125	94	1.54
35	120	112	82	94	90	56	150	114	1.11
50	146	137	99	112	109	-	178	136	0.829
70	185	172	123	142	138	-	219	170	0.583
95	228	213	150	177	170	-	263	208	0.431
120	265	247	172	202	198	-	300	237	0.351
150	303	282	194	228	226	-	336	266	0.296
185	348	324	220	263	259	-	379	304	0.251
240	412	383	256	316	307	-	438	359	0.210
300	472	438	288	-	-	-	493	404	0.186
400	544	504	326	-	-	-	557	468	0.168
500	616	571	363	-	-	-	620	522	0.156

Note:

Refer to Cable Selection in Technical Cable Guide for more information and data based on AS/NZS 3008.1.1.

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group; any modification or alteration afterwards of product may give different result. The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.

