




### **MEDIUM VOLTAGE CABLES**

## Aluminium 19/33 kV - Three core heavy duty screened armoured





### **Application**

Electricity distribution or sub-transmission networks cable typically used as primary supply to Commercial, Industrial and urban residential networks. Suitable for high fault level systems rated up to 10kA/1sec. Higher fault current rated constructions are available on request.

#### Approvals

Approved by all major power Utilities and industrial customers in Australia.

## Behaviour in flame and fire:

PVC or LSOH outer sheath exceeds the requirements of IEC 60332-1.

### Temperature range

Minimum installation temperature: 0 °C Maximum operating temperature: +90 °C Minimum operating temperature: -25 °C

## Minimum bending radius

Installed cables: 12D (PVC only)

15D (HDPE)

During installation: 18D (PVC only)

25D (HDPE)

### Resistance to

Chemical exposure: Accidental

Mechanical impact: Heavy (Armoured)

Water exposure: XLPE - Spray

EPR - Immersion/Temporary coverage

Solar radiation and

weather exposure: Suitable for direct exposure.

### Cable design

### Conductor:

Circular compacted aluminium

#### Conductor screen:

Extruded semi-conductive compound, bonded to the insulation and applied in the same operations as the insulation

### Insulation:

Cross Linked Polyethylene (XLPE) – standard Ethylene Propylene Rubber (EPR) – alternative

## Insulation screen:

Extruded, semi-conductive compound

## Metallic screen:

Plain annealed copper wire: nominal 10kA for 1 second. See table next page.

## Armouring:

Galvanised steel wires

## Sheath:

Black 5V-90 polyvinyl chloride (PVC) – standard Orange 5V-90 PVC inner plus black high density polyethylene (HDPE) outer – alternative Low smoke zero halogen (LSOH) – alternative

## **Installation conditions**

In free air In duct In trench In ground

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group: any modification or alteration afterwards of product may give different result. The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.





## **MEDIUM VOLTAGE CABLES**

# Physical & Electrical Characteristics

			Aluminium	1 19/33 kV - T	hree core hea	ıvy duty scree	ned armoured		
Product	code: 3CALX33H	IDA							
Nominal conductor area mm²		50	70	95	120	150			
Nominal conductor diameter mm		8.1	9.8	11.5	12.9	14.2			
Nominal thicknes	insulation s mm	8.0	8.0	8.0	8.0	8.0			
Approx c		80.0	84.1	88.0	91.3	94.6			
Approx n kg/100m		835	920	1010	1080	1150			
Max pulling tension on conductors kN		7.5	11	14	18	23			
	ing tension ing grip kN	7.5	11	14	18	23			
Max pulling tension on amour wires kN		25	25	25	25	25			
Min bending radius* during installation mm		1440	1510	1580	1640	1700			
Min bending radius* set in position mm		960	1010	1060	1100	1140			
Max conductor resistance, dc @ 20°C Ohm/km		0.641	0.443	0.320	0.253	0.206			
Conductor resistance, ac @ 90°C & 50 Hz Ohm/km		0.822	0.568	0.411	0.325	0.265			
Inductance mH/km		0.457	0.422	0.401	0.387	0.375			
Inductive reactance, @ 50Hz Ohm/km		0.144	0.133	0.126	0.121	0.118			
Zero seq. impedance @ 20°C & 50 Hz Ohm/km		2.46+ j0.0981	1.76+ j0.0871	1.28+ j0.0805	1.09+ j0.0762	1.05+ j0.0724			
Capacitance, phase to earth µF/km		0.139	0.155	0.171	0.183	0.196			
Min insulation resistance @ 20°C MOhm.km		18,000	16,000	15,000	14,000	13,000			
Electric stress at conductor screen kV/mm		4.08	3.85	3.67	3.56	3.46			
Charging current @ rated voltage & 50 Hz A/phase/km		0.831	0.927	1.02	1.09	1.17			
Short circuit rating	Phase conductor kA,1 sec	4.7	6.6	9.0	11.3	14.2			
	Metallic screen kA, 1 sec	4.6	6.3	8.6	10	10			
Contin- uous current rating	In ground, direct buried A	145	190	225	255	285			
	In ground, in singleway ducts A	130	160	195	225	250			
	In free air, unenclosed & spaced from wall A	150	185	235	270	305			

The cables described are designed to be used for the supply of electrical energy in fixed applications up to the rated voltages at a nominal power frequency between 49Hz and 61Hz. All values are for XLPE cables only. \*Increased radius required for HDPE and nylon incorporating designs.