




MEDIUM VOLTAGE CABLES

Aluminium 6.35/11 kV - Three core light duty screened unarmoured





Application

Electricity distribution network cable typically used as primary supply to Commercial, Industrial and urban residential networks. Suitable for low fault level or fast fault clearing cable systems.

Approvals

Approved by all major power Utilities and industrial customers in Australia.

Behaviour in flame and fire:

PVC or LSOH outer sheath exceeds the requirements of IEC 60332-1.

Temperature range

Minimum installation temperature: 0°C Maximum operating temperature: +90°C Minimum operating temperature: -25°C

Minimum bending radius

Installed cables: 12D (PVC only)

15D (HDPE)

During installation: 18D (PVC only)

25D (HDPE)

Resistance to

Chemical exposure: Accidental

Mechanical impact: Light (PVC only)

Heavy (HDPE)

Water exposure: XLPE - Spray

EPR - Immersion/Temporary coverage

Solar radiation and

weather exposure: Suitable for direct exposure.

Cable design

Conductor:

Circular compacted aluminium

Conductor screen:

Extruded semi-conductive compound, bonded to the insulation and applied in the same operations as the insulation.

Insulation:

Cross Linked Polyethylene (XLPE) – standard Ethylene Propylene Rubber (EPR) – alternative

Insulation screen:

Extruded, semi-conductive compound

Metallic screen:

Plain annealed copper wire: nominal 3kA for 1 second. See table next page.

Sheath:

Black 5V-90 polyvinyl chloride (PVC) – standard Orange 5V-90 PVC inner plus black high density polyethylene (HDPE) outer – alternative Low smoke zero halogen (LSOH) – alternative

Installation conditions

In free air In duct In trench

In ground with protection

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group: any modification or alteration afterwards of product may give different result. The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.





MEDIUM VOLTAGE CABLES

Physical & Electrical Characteristics

Aluminium 6.35/11 kV – Three core light duty screened unarmoured											
Product code: 3CALX11LD											
Nominal conductor area mm²		25	35	50	70	95	120	150	185	240	300
Nominal conductor diameter mm		6.1	7.1	8.1	9.8	11.5	12.9	14.2	16.0	18.1	20.6
Nominal insulation thickness mm		3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
Approx cable diameter mm		42.3	44.8	47.2	51.2	55.1	58.2	61.3	65.3	70.3	76.3
Approx mass kg/100m		140	160	185	220	265	295	340	390	465	550
Max pulling tension on conductors kN		3.8	5.3	7.5	11	14	18	23	25	25	25
Max pulling tension on stocking grip kN		3.8	5.3	7.5	9.2	11	12	13	15	17	20
Min bending radius* during installation mm		760	810	850	920	990	1050	1100	1170	1270	1370
Min bending radius* set in position mm		510	540	570	610	660	700	740	780	840	920
Max conductor resistance, dc @ 20°C Ohm/km		1.20	0.868	0.641	0.443	0.320	0.253	0.206	0.164	0.125	0.100
Conductor resistance, ac @ 90°C & 50 Hz Ohm/km		1.54	1.11	0.822	0.568	0.411	0.325	0.265	0.211	0.162	0.130
Inductance mH/km		0.416	0.396	0.380	0.350	0.333	0.322	0.313	0.300	0.290	0.282
Inductive reactance, @ 50Hz Ohm/km		0.131	0.124	0.119	0.110	0.105	0.101	0.0983	0.0944	0.0912	0.0885
Zero seq. impedance @ 20°C & 50 Hz Ohm/km		4.48+ j0.0839	3.60+ j0.0777	3.37+ j0.0728	2.97+ j0.0635	2.66+ j0.0585	2.44+ j0.0553	2.26+ j0.0525	2.09+ j0.0487	1.95+ j0.0456	1.74+ j0.0431
Capacitance, phase to earth µF/km		0.211	0.233	0.254	0.290	0.325	0.353	0.381	0.417	0.462	0.518
Min insulation resistance @ 20°C MOhm.km		12,000	11,000	10,000	8,900	7,900	7,200	6,600	6,000	5,400	4,900
Electric stress at conductor screen kV/mm		2.65	2.56	2.49	2.40	2.33	2.29	2.25	2.22	2.18	2.14
Charging current @ rated voltage & 50 Hz A/phase/km		0.420	0.465	0.507	0.578	0.648	0.704	0.760	0.833	0.921	1.03
Short circuit rating	Phase conductor kA, 1 sec	2.4	3.3	4.7	6.6	9.0	11.3	14.2	17.5	22.7	28.3
	Metallic screen kA, 1 sec	2.5	3.0	3.0	3.3	3.5	3.8	4.0	4.3	4.6	5.1
Contin- uous current rating	In ground, direct buried A	110	130	155	185	220	250	285	325	370	420
	In ground, in singleway ducts A	95	110	130	160	185	215	245	275	320	360
	In free air, unenclosed & spaced from wall A	105	125	145	180	220	255	290	340	400	460

The cables described are designed to be used for the supply of electrical energy in fixed applications up to the rated voltages at a nominal power frequency between 49Hz and 61Hz. All values are for XLPE cables only. *Increased radius required for HDPE and nylon incorporating designs.