

CONSTRUCTION - PVC CABLES 0.6 /1 kV

CONTROL 1.5MM² 2-50C+E

PVC INSULATED LAID UP AND SHEATHED CONTROL CABLE TO AS/NZS 5000.1.

For control circuits unenclosed, enclosed in conduit, buried direct or in underground ducts for commercial, industrial, mining and electricity authority systems where not subject to mechanical damage.



Cable Characteristics

Semi-rigid	OD≤25 4D OD>25 6D	1	Water Drops	Good	+75 °C -15 °C	C3	Good

Cable Design

CONDUCTOR:

Plain annealed copper conductor to AS/NZS 1125
Maximum continuous operating temperature: 75 °C

Can also be operated at temperatures up to 90 °C when not exposed to mechanical deformation (see AS/NZS 3008.1)

INSULATION:

V-90 PVC
Colours: White with Black numbering, Green/Yellow

SHEATH:

5V-90 PVC
Colours: Orange, Black

Installation Conditions

INDUSTRIAL EQUIPMENT	OD≤25 6D OD>25 9D	IN FREE AIR	IN CONDUIT	MACHINES	0 °C	IN TRENCH	IN GROUND WITH PROTECTION	IN DUCT

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group; any modification or alteration afterwards of product may give different result. The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.



Physical & Electrical Characteristics

Product code	Cable						Min. installed bending radius mm
	Conductor nominal C.S.A. mm ²	Number of cores	Nominal insulation thickness mm	Overall diameter		Approx. mass kg/100 m	
				Minimum mm	Maximum mm		
1.52CECON	1.5	2	0.8	10.0	10.5	15	40
1.53CECON	1.5	3	0.8	10.9	11.3	18	50
1.54CECON	1.5	4	0.8	11.8	12.2	22	50
1.55CECON	1.5	5	0.8	13.0	13.5	23	60
1.56CECON	1.5	6	0.8	13.0	13.5	27	60
1.57CECON	1.5	7	0.8	15.1	15.5	30	60
1.58CECON	1.5	8	0.8	16.0	16.5	34	70
1.510CECON	1.5	10	0.8	16.3	16.7	37	70
1.512CECON	1.5	12	0.8	16.8	17.3	42	70
1.515CECON	1.5	15	0.8	18.4	19.0	50	80
1.520CECON	1.5	20	0.8	21.3	21.8	64	90
1.525CECON	1.5	25	0.8	22.5	23.0	75	100
1.530CECON	1.5	30	0.8	24.6	25.2	87	160
1.540CECON	1.5	40	0.8	27.5	28.0	112	170
1.550CECON	1.5	50	0.8	30.2	30.8	136	190

Number of cores	Current rating (a)			Electrical characteristics	
	Unenclosed spaced A	Buried direct A	Underground in duct A	Maximum D.C. resistance at 20°C Ω/km	Reactance per core Ω/km
2	19	28	22	13.6	0.111
3	16	24	19	13.6	0.111
4	16	24	19	13.6	0.111
5	14	24	14	13.6	0.111
6	13	22	13	13.6	0.111
7	13	22	13	13.6	0.111
8	12	21	12	13.6	0.111
10	11	19	11	13.6	0.111
12	11	18	11	13.6	0.111
15	10	17	10	13.6	0.111
20	9	15	9	13.6	0.111
25	8	14	8	13.6	0.111
30	8	13	8	13.6	0.111
40	7	12	7	13.6	0.111
50	7	12	7	13.6	0.111

(a) Based on 75 °C conductor temperature, 40 °C ambient air temperature and where applicable, burial depth of 0.5 m, soil temperature of 25 °C and soil thermal resistivity of 1.2 °C.m/W. Refer to AS/NZS 3008.1 for other installation conditions.

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group; any modification or alteration afterwards of product may give different result. The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.



CABLE HANDLING

Cable Usage Characteristics



AMBIENT TEMPERATURE

Maximum operating temperature
Minimum operating temperature



MECHANICAL IMPACT RESISTANCE

1	Light Impact
2	Moderate Impact
3	Heavy Impact
4	Very Heavy Impact



RESISTANCE TO SOLAR RADIATION AND WEATHER

Excellent	Permanent
Very Good	Frequent
Good	Occasional
Acceptable	Accidental
Poor	None



BEHAVIOUR IN FLAME AND FIRE

Reaction To Fire	Resistant To Fire
C 1 Fire retardant	Level 1 Ultimate fire survival
C 2 Flame retardant	Level 2 Two hours fire survival
C 3 No fire performance	Level 3 Restrained spread & self extinguishing



HALOGEN FREE

AS/NZS 4507



MINIMUM BENDING RADIUS

Minimum bending radius of installed cables



CHEMICAL RESISTANCE

Excellent	Permanent
Very Good	Frequent
Good	Occasional
Acceptable	Accidental
Poor	None



RESISTANCE TO WATER

Negligible	No humidity
Water Drops	Occasional condensation
Spray	Water run off
Splashes	Exposed to water splashes
Heavy Sea	Exposed to waves
Immersion	Temporarily covered by water
Submersion	Permanently covered by water



FLEXIBILITY


Rigid	Flexible
Semi-rigid	Very flexible




LOW SMOKE EMISSION

AS/NZS 4507


Laying Conditions




MINIMUM BENDING RADIUS DURING INSTALLATION



IN TRENCH




IN GROUND




IN DUCT




DOMESTIC APPLIANCES




MACHINES




MOBILE EQUIPMENT




SUBMERGED




OVERHEAD AERIAL




MIN. INSTALLATION TEMPERATURE



IN FREE AIR



IN GROUND WITH PROTECTION



IN CONDUIT



OUTDOOR APPLIANCES



FESTOON



INTERNAL WIRING



INDUSTRIAL EQUIPMENT



EXTERNAL BUILDING

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group; any modification or alteration afterwards of product may give different result. The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.

