



MEDIUM VOLTAGE CABLES

Aluminium 19/33 kV - Single core light duty screened unarmoured





Application

Electricity distribution or sub-transmission networks cable typically used as primary supply to Commercial, Industrial and urban residential networks. Suitable for low fault level or fast fault clearing cable systems.

Approvals

Approved by all major power Utilities and industrial customers in Australia.

Behaviour in flame and fire:

PVC or LSOH outer sheath exceeds the requirements of IEC 60332-1.

Temperature range

Minimum installation temperature: 0°C Maximum operating temperature: +90°C Minimum operating temperature: -25°C

Minimum bending radius

Installed cables: 12D (PVC only)

15D (HDPE)

During installation: 18D (PVC only)

25D (HDPE)

Resistance to

Chemical exposure: Accidental

Mechanical impact: Light (PVC only)

Heavy (HDPE)

Water exposure: XLPE - Spray

EPR - Immersion/Temporary coverage

Solar radiation and

weather exposure: Suitable for direct exposure.

Cable design

Conductor:

Circular compacted aluminium

Conductor screen:

Extruded semi-conductive compound, bonded to the insulation and applied in the same operations as the insulation.

Insulation:

Cross Linked Polyethylene (XLPE) – standard Ethylene Propylene Rubber (EPR) – alternative

Insulation screen:

Extruded, semi-conductive compound

Metallic screen:

Plain annealed copper wire: nominal 3kA for 1 second. See table next page.

Sheath:

Black 5V-90 polyvinyl chloride (PVC) – standard Orange 5V-90 PVC inner plus black high density polyethylene (HDPE) outer – alternative Low smoke zero halogen (LSOH) – alternative

Installation conditions

In free air In duct In trench

In ground with protection

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group: any modification or alteration afterwards of product may give different result. The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.





MEDIUM VOLTAGE CABLES

Physical & Electrical Characteristics

			Alun	ninium 19/	33 kV – Si	ngle core l	ight duty	screened ι	ınarmoure	ed			
Product of	code: 1CALX33L	D											
Nominal conductor area mm²		50	70	95	120	150	185	240	300	400	500	630	
Nominal conductor diameter mm		8.1	9.8	11.5	12.9	14.2	16.0	18.1	20.6	23.5	26.6	30.2	
Nominal insulation thickness mm		8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0	
Approx cable diameter mm		33.0	34.7	36.6	38.0	39.5	41.3	43.6	46.5	50.2	53.5	57.3	
Approx mass kg/100m		110	120	135	150	165	180	205	235	275	320	375	
Max pulling tension on conductor kN		2.5	3.5	4.8	6.0	7.5	9.3	12	15	20	25	25	
Max pulling tension on stocking grip kN		2.5	3.5	4.7	5.0	5.5	6.0	6.7	7.6	8.8	10	11	
Min bending radius* during installation mm		590	630	660	680	710	740	790	840	900	960	1030	
Min bending radius* set in position mm		400	420	440	460	470	500	520	560	600	640	690	
Max conductor resistance, dc @ 20°C Ohm/km		0.641	0.443	0.320	0.253	0.206	0.164	0.125	0.100	0.0778	0.0605	0.0469	
Conductor resistance, ac @ 90°C & 50 Hz Ohm/km		0.822	0.568	0.411	0.325	0.265	0.211	0.161	0.129	0.101	0.0797	0.0630	
Inductance, trefoil touching mH/km		0.508	0.469	0.447	0.431	0.419	0.401	0.386	0.372	0.361	0.348	0.336	
Inductive reactance, trefoil touching @ 50Hz Ohm/km		0.160	0.147	0.140	0.136	0.132	0.126	0.121	0.117	0.113	0.109	0.105	
Zero seq. impedance @ 20°C & 50 Hz Ohm/km		1.57+ j0.0978	1.38+ j0.0868	1.25+ j0.0802	1.19+ j0.0759	1.14+ j0.0722	1.10+ j0.0672	1.06+ j0.0629	1.03+ j0.0591	1.01+ j0.0561	0.996+ j0.0526	0.982+ j0.0492	
Capacitance, phase to earth µF/km		0.139	0.155	0.170	0.183	0.195	0.211	0.230	0.254	0.284	0.312	0.344	
Min insulation resistance @ 20°C MOhm.km		18,000	16,000	15,000	14,000	13,000	12,000	11,000	9,900	8,800	8,000	7,200	
Electric stress at conductor screen kV/mm		4.08	3.85	3.67	3.56	3.46	3.36	3.26	3.16	3.06	2.99	2.93	
Charging current @ rated voltage & 50 Hz A/phase/km		0.828	0.923	1.02	1.09	1.16	1.26	1.37	1.52	1.70	1.86	2.05	
Short circuit rating	Phase conductor kA,1sec	4.7	6.6	9.0	11.3	14.2	17.5	22.7	28.3	37.8	47.2	59.5	
	Metallic screen kA,1sec	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	
Contin- uous current rating	In ground, direct buried A	160	195	230	265	295	330	385	435	495	565	645	
	In ground, in singleway ducts A	155	190	225	255	285	320	370	415	470	535	605	
	In free air, unenclosed & spaced from wall A	170	215	260	295	335	385	455	520	610	705	820	

The cables described are designed to be used for the supply of electrical energy in fixed applications up to the rated voltages at a nominal power frequency between 49Hz and 61Hz. All values are for XLPE cables only. *Increased radius required for HDPE and nylon incorporating designs.