

Properties of BendBright™ XS Single-Mode Fibre

SM_G.657.A2 BBXS (C24)



APPLICABLE STANDARDS

- IEC / EN 60793-2-50 Category B-657.A2 and B-652.D
- ITU Recommendation G.657.A2 and G.657.B2
- ITU-T Recommendation G.652.D
- EN 50 173-1: Category OS2 and OS1a
- ISO / IEC 11801: Category OS2 and OS1a
- All measurements are in accordance with ITU-T G.650 Recommendation

ATTENUATION IN CABLE

Attribute	Measurement method	Units	Limits
Maximum attenuation in cable at 1310 nm	IEC/EN 60793-1-40	dB/km	≤ 0.38
Maximum attenuation in cable at 1383 nm ⁽¹⁾	IEC/EN 60793-1-40	dB/km	≤ 0.38
Maximum attenuation in cable at 1550 nm	IEC/EN 60793-1-40	dB/km	≤ 0.23
Maximum attenuation in cable at 1625 nm	IEC/EN 60793-1-40	dB/km	≤ 0.25
Local discontinuity at 1310 and 1550 nm	IEC/EN 60793-1-40	dB	max. 0.1

(1) including H2-ageing according to IEC 60793-2-50, type B1.3, at 1383 nm.

OPTICAL PROPRIETIES OF FIBRE

Attribute	Measurement method	Units	Limits
Mode field diameter at 1310 nm	IEC/EN 60793-1-45	μm	8.8 ± 0.4
Mode field diameter at 1550 nm	IEC/EN 60793-1-45	μm	9.8 ± 0.5
Chromatic Dispersion coefficient:	IEC/EN 60793-1-42		
• in the interval 1285 nm – 1330 nm		ps/km · nm	$\leq 3.7 $
• at 1550 nm		ps/km · nm	≤ 18.5
• at 1625 nm		ps/km · nm	≤ 23.0
Zero Dispersion Wavelength, λ_0		nm	1300 - 1324
Zero Dispersion Slope		ps/(nm ² · km)	≤ 0.092
Cut-off Wavelength, λ_{cc}	IEC/EN 60793-1-44	nm	≤ 1260 ⁽²⁾
Polarisation Mode Dispersion (PMD) coefficient	IEC/EN 60793-1-48	ps/√km	≤ 0.1 ⁽³⁾
PMD _Q Link Design Value (computed with Q=0.01%, N=20)	IEC/EN 60794-3	ps/√km	≤ 0.06 ⁽³⁾

(2) guaranteed value according to the ITU-T (ATM G650) method.

(3) PMD may change when fibre is cabled.

ATTENUATION VARIATION VS BENDING

Attribute	Measurement method	Units	Limits
10 turns on a mandrel R = 15 mm at 1550 nm	IEC/EN 60793-1-47	dB	≤ 0.03
10 turns on a mandrel R = 15 mm at 1625 nm	IEC/EN 60793-1-47	dB	≤ 0.1
1 turn on a mandrel R = 10 mm at 1550 nm	IEC/EN 60793-1-47	dB	≤ 0.1
1 turn on a mandrel R = 10 mm at 1625 nm	IEC/EN 60793-1-47	dB	≤ 0.2
1 turn on a mandrel R = 7.5 mm at 1550 nm	IEC/EN 60793-1-47	dB	≤ 0.5
1 turn on a mandrel R = 7.5 mm at 1625 nm	IEC/EN 60793-1-47	dB	≤ 1.0

GROUP INDEX OF REFRACTION

Attribute	Measurement method	Units	Limits
1310 nm	IEC/EN 60793-1-22	-	1.467
1550 nm	IEC/EN 60793-1-22	-	1.467
1625 nm	IEC/EN 60793-1-22	-	1.468

RAYLEIGH BACKSCATTER COEFFICIENT (INS PULSE WIDTH)

Attribute	Measurement method	Units	Limits
1310 nm	-	dB	-79.1
1550 nm	-	dB	-81.4
1625 nm	-	dB	-82.2

GEOMETRICAL PROPERTIES

Attribute	Measurement method	Units	Limits
Cladding diameter	IEC/EN 60793-1-20	μm	125.0 ± 0.7
Cladding non-Circularity	IEC/EN 60793-1-20	%	≤ 0.7
Core-Cladding Concentricity error	IEC/EN 60793-1-20	μm	≤ 0.5
Coating diameter - ColorLock® XS and Natural	IEC/EN 60793-1-21	μm	245 ± 10
Coating non-Circularity	IEC/EN 60793-1-21	%	≤ 5
Coating-Cladding Concentricity error	IEC/EN 60793-1-21	μm	≤ 12

MECHANICAL PROPERTIES

Attribute	Measurement method	Units	Limits
Proof stress level	IEC/EN 60793-1-30	GPa	≥ 0.7 ($\approx 1\%$)
Strip force (peak)	IEC/EN 60793-1-32	N	$1.2 \leq F_{\text{peak,strip}} \leq 8.9$
Dynamic Fatigue Resistance, aged and unaged	IEC/EN 60793-1-33	-	$n_d \geq 20$

© PRYSMIAN 2026, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted, or reproduced in any form, either wholly or in part, without the written consent of Prysmian. The information is believed to be correct at the time of issue. Prysmian reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian.